


RE 13 Ø13 mm, precious metal brushes, 2 watt

RE



M 1:1

- Stock program
- Standard program
- Special program (on request)

Part Numbers


Motor Data	118491	118492	118493	118494	118495	118496	118497	118498	118499	118500	118501	118502	118503	118504	118505
------------	--------	--------	--------	--------	--------	--------	--------	--------	--------	--------	--------	--------	--------	--------	--------

Motor Data	118491	118492	118493	118494	118495	118496	118497	118498	118499	118500	118501	118502	118503	118504	118505	
Values at nominal voltage																
1 Nominal voltage	V	1.5	1.5	1.8	2.4	3	3	3.6	4.2	4.8	6	7.2	9	10	12	15
2 No load speed	rpm	6570	6090	6380	7170	7100	6300	6800	6620	6490	6810	6590	6630	6840	7020	7150
3 No load current	mA	43.8	39.8	35.3	30.8	24.3	20.8	19.2	15.8	13.5	11.5	9.19	7.41	6.94	5.99	4.91
4 Nominal speed	rpm	5170	4320	4160	4400	3560	2550	3000	2880	2880	3130	2880	2940	3120	3330	3400
5 Nominal torque	mNm	1.46	1.58	1.82	2.18	2.78	2.91	2.85	2.91	3.02	2.95	2.93	2.94	2.92	2.93	2.88
6 Nominal current (max. continuous current)	A	0.72	0.72	0.72	0.72	0.72	0.669	0.592	0.502	0.446	0.367	0.294	0.237	0.218	0.188	0.151
7 Stall torque	mNm	6.22	5.12	5.01	5.5	5.51	4.86	5.1	5.16	5.46	5.49	5.26	5.34	5.42	5.63	5.54
8 Stall current	A	2.89	2.21	1.89	1.75	1.39	1.09	1.03	0.866	0.786	0.665	0.514	0.419	0.395	0.351	0.282
9 Max. efficiency	%	77	75	75	76	76	75	75	75	76	76	75	76	76	76	76
Characteristics																
10 Terminal resistance	Ω	0.519	0.679	0.951	1.37	2.16	2.75	3.5	4.85	6.11	9.03	14	21.5	25.3	34.2	53.2
11 Terminal inductance	mH	0.021	0.025	0.032	0.046	0.073	0.092	0.114	0.164	0.223	0.316	0.485	0.749	0.87	1.19	1.79
12 Torque constant	mNm/A	2.15	2.31	2.65	3.14	3.97	4.46	4.96	5.95	6.94	8.27	10.2	12.7	13.7	16	19.7
13 Speed constant	rpm/V	4440	4130	3610	3040	2410	2140	1930	1600	1380	1160	932	750	696	595	485
14 Speed / torque gradient	rpm/mNm	1070	1210	1300	1330	1310	1320	1360	1310	1210	1260	1270	1260	1280	1270	1310
15 Mechanical time constant	ms	7.65	7.55	7.45	7.37	7.28	7.27	7.28	7.23	7.16	7.2	7.21	7.21	7.21	7.22	7.27
16 Rotor inertia	gcm ²	0.681	0.596	0.548	0.53	0.53	0.526	0.512	0.528	0.565	0.545	0.541	0.544	0.536	0.543	0.529

Specifications Operating Range Comments

- Thermal data**
- 17 Thermal resistance housing-ambient 46 K/W
 - 18 Thermal resistance winding-housing 14 K/W
 - 19 Thermal time constant winding 5.18 s
 - 20 Thermal time constant motor 76.1 s
 - 21 Ambient temperature -20...+65°C
 - 22 Max. winding temperature +85°C

- Mechanical data (sleeve bearings)**
- 23 Max. speed 11 000 rpm
 - 24 Axial play 0.05 - 0.15 mm
 - 25 Radial play 0.014 mm
 - 26 Max. axial load (dynamic) 0.8 N
 - 27 Max. force for press fits (static) 15 N (static, shaft supported)
 - 28 Max. radial load, 5 mm from flange 170 N



- **Continuous operation**
In observation of above listed thermal resistance (lines 17 and 18) the maximum permissible winding temperature will be reached during continuous operation at 25°C ambient.
= Thermal limit.
- Short term operation**
The motor may be briefly overloaded (recurring).
- **Assigned power rating**

Other specifications Modular System Details on catalog page 44

- Other specifications**
- 29 Number of pole pairs 1
 - 30 Number of commutator segments 7
 - 31 Weight of motor 12 g

Values listed in the table are nominal.
Explanation of the figures on page 90.

Sensor	Motor Control
472_ENX 13 GAMA	532_ESCON Module 24/2
504_Encoder MR 16 CPT	532_ESCON 36/2 DC
505_Encoder MR 64-256 CPT	541_EPOS4 Micro 24/5
506_Encoder MR 64-256 CPT	542_EPOS4 Module 24/1.5
	543_EPOS4 Compact 24/5 3-axes
	544_EPOS4 Compact 24/1.5