


RE 16 \varnothing 16 mm, precious metal brushes CLL, 3.2 watt

RE



M 1:1

- Stock program
- Standard program
- Special program (on request)

Part Numbers														
118678	118679	118680	118681	118682	118683	118684	118685	118686	118687	118688	118689	118690	118691	118692

Motor Data		118678	118679	118680	118681	118682	118683	118684	118685	118686	118687	118688	118689	118690	118691	118692
Values at nominal voltage																
1 Nominal voltage	V	1.8	2.4	3	3.2	4.5	4.8	7.2	9	12	12	15	18	24	30	48
2 No load speed	rpm	4990	6360	6890	6270	6740	5700	6890	6740	7130	5990	6010	5900	7250	6460	5500
3 No load current	mA	23.5	25.4	23	18.6	14.8	10.8	9.57	7.4	6.05	4.63	3.72	3.02	3.11	2.08	1.02
4 Nominal speed	rpm	4320	5510	5820	4930	5050	3630	4810	4630	5030	3830	3840	3730	5070	4220	3180
5 Nominal torque	mNm	2.39	2.5	2.89	3.41	4.48	5.61	5.54	5.48	5.48	5.38	5.36	5.33	5.29	5.18	5.01
6 Nominal current (max. continuous current)	A	0.72	0.72	0.72	0.72	0.72	0.711	0.566	0.438	0.348	0.287	0.229	0.187	0.171	0.119	0.0614
7 Stall torque	mNm	15.5	16.9	17.3	15.2	17.4	15.2	18.1	17.4	18.6	14.9	14.9	14.5	17.6	15	11.9
8 Stall current	A	4.53	4.71	4.19	3.13	2.74	1.9	1.82	1.37	1.16	0.784	0.628	0.5	0.561	0.341	0.144
9 Max. efficiency	%	86	86	86	85	86	86	86	86	86	86	85	85	86	85	84
Characteristics																
10 Terminal resistance	Ω	0.397	0.51	0.715	1.02	1.64	2.53	3.95	6.56	10.3	15.3	23.9	36	42.8	88	333
11 Terminal inductance	mH	0.021	0.023	0.03	0.042	0.071	0.113	0.174	0.284	0.452	0.639	0.993	1.48	1.75	3.44	12.1
12 Torque constant	mNm/A	3.43	3.58	4.13	4.84	6.34	7.99	9.92	12.7	16	19	23.7	28.9	31.4	44.1	82.7
13 Speed constant	rpm/V	2790	2660	2310	1970	1510	1190	962	753	597	502	403	330	304	217	115
14 Speed/torque gradient	rpm/mNm	323	379	400	415	391	378	383	389	386	404	406	410	414	432	465
15 Mechanical time constant	ms	5.84	5.71	5.56	5.46	5.36	5.31	5.29	5.29	5.27	5.29	5.3	5.31	5.31	5.36	5.42
16 Rotor inertia	gcm ²	1.73	1.44	1.33	1.26	1.31	1.34	1.32	1.3	1.3	1.25	1.25	1.24	1.23	1.18	1.11

Specifications	Operating Range	Comments
Thermal data 17 Thermal resistance housing-ambient 30 K/W 18 Thermal resistance winding-housing 8.5 K/W 19 Thermal time constant winding 10.6 s 20 Thermal time constant motor 436 s 21 Ambient temperature -20...+65°C 22 Max. winding temperature +85°C		<p> Continuous operation In observation of above listed thermal resistance (lines 17 and 18) the maximum permissible winding temperature will be reached during continuous operation at 25°C ambient. = Thermal limit.</p> <p> Short term operation The motor may be briefly overloaded (recurring).</p> <p> Assigned power rating</p>
Mechanical data (sleeve bearings) 23 Max. speed 11 000 rpm 24 Axial play 0.05 - 0.15 mm 25 Radial play 0.014 mm 26 Max. axial load (dynamic) 0.8 N 27 Max. force for press fits (static) 15 N 28 Max. radial load, 5 mm from flange 1.5 N		

Other specifications	Modular System	Details on catalog page 44
29 Number of pole pairs 1 30 Number of commutator segments 7 31 Weight of motor 38 g CLL = Capacitor Long Life	Gear 405_GP 16 A 406_GP 16 C 447-449_GP 16 S	Motor Control 532_ESCON Module 24/2 532_ESCON 36/2 DC 533_ESCON Module 50/5 535_ESCON 50/5

Values listed in the table are nominal.
 Explanation of the figures on page 90.