



RE 13 Ø13 mm, graphite brushes, 3 watt



M 1:1

- Stock program
- Standard program
- Special program (on request)

Part numbers

118628 118629 118630 118631 118632 118633 118634 118635 118636 118637 118638 118639 118640 118641 118642

Motor data																	
Values at nominal voltage																	
1 Nominal voltage	V	3	3.6	3.6	4.8	6	6	7.2	9	10	12	15	18	21	24	30	
2 No load speed	rpm	12000	13600	11900	13600	13600	12100	13100	13800	13200	13300	13400	13000	14100	13800	14000	
3 No load current	mA	168	164	136	121	95.5	81	75.3	64	53.9	45.4	36.8	29.2	28	23.8	19.5	
4 Nominal speed	rpm	9520	10800	8780	10100	10300	8660	9790	10600	10100	10200	10400	9910	11100	10800	11000	
5 Nominal torque	mNm	1.22	1.32	1.58	1.92	2.05	2.17	2.12	2.17	2.32	2.3	2.31	2.36	2.29	2.33	2.28	
6 Nominal current (max. continuous current)	A	0.72	0.72	0.72	0.72	0.602	0.558	0.495	0.422	0.383	0.319	0.259	0.212	0.192	0.167	0.134	
7 Stall torque	mNm	7.44	8.13	7.11	8.58	9.25	8.35	9.03	10.1	10.5	10.4	10.5	10.4	11.1	11	10.9	
8 Stall current	A	3.46	3.51	2.69	2.73	2.33	1.87	1.82	1.69	1.52	1.25	1.03	0.814	0.809	0.688	0.556	
9 Max. efficiency	%	50	53	53	57	60	60	61	63	64	65	65	66	66	66	66	
Characteristics																	
10 Terminal resistance	Ω	0.867	1.02	1.34	1.76	2.57	3.21	3.96	5.32	6.6	9.56	14.6	22.1	26	34.9	54	
11 Terminal inductance	mH	0.021	0.025	0.032	0.046	0.073	0.092	0.114	0.164	0.223	0.316	0.486	0.75	0.871	1.19	1.79	
12 Torque constant	mNm/A	2.15	2.31	2.65	3.14	3.97	4.46	4.96	5.95	6.94	8.27	10.2	12.7	13.7	16	19.7	
13 Speed constant	rpm/V	4440	4130	3610	3040	2410	2140	1930	1600	1380	1160	932	750	696	595	485	
14 Speed / torque gradient	rpm/mNm	1790	1830	1830	1700	1560	1540	1430	1310	1340	1330	1300	1320	1320	1300	1330	
15 Mechanical time constant	ms	12.8	11.4	10.5	9.44	8.68	8.46	8.23	7.93	7.74	7.62	7.51	7.42	7.39	7.37	7.38	
16 Rotor inertia	gcm ²	0.681	0.596	0.548	0.53	0.53	0.526	0.512	0.528	0.565	0.545	0.541	0.544	0.536	0.543	0.529	

Specifications	Operating range	Comments
Thermal data 17 Thermal resistance housing-ambient 33 K/W 18 Thermal resistance winding-housing 7.0 K/W 19 Thermal time constant winding 4.88 s 20 Thermal time constant motor 259 s 21 Ambient temperature -20...+65°C 22 Max. winding temperature +85°C Mechanical data (sleeve bearings) 23 Max. speed 16 000 rpm 24 Axial play 0.05 - 0.15 mm 25 Radial play 0.014 mm 26 Max. axial load (dynamic) 0.8 N 27 Max. force for press fits (static) 15 N (static, shaft supported) 95 N 28 Max. radial load, 5 mm from flange 1.4 N	n [rpm] 	Continuous operation In observation of above listed thermal resistance (lines 17 and 18) the maximum permissible winding temperature will be reached during continuous operation at 25°C ambient. = Thermal limit. Short term operation The motor may be briefly overloaded (recurring). Assigned power rating

Other specifications	Modular system	Details on catalog page 48
29 Number of pole pairs 1 30 Number of commutator segments 7 31 Weight of motor 27 g Values listed in the table are nominal. Explanation of the figures on page 94.	Gear 415_GP 13 A Sensor 498_ENX 13 GAMA 501_ENX 13 IMR 532_Encoder MR 16 CPT	Motor Control 550_ESCON Module 24/2 550_ESCON 36/2 DC 551_ESCON Module 50/5 553_ESCON 50/5 557_ESCON2 Nano 24/2 557_ESCON2 Micro 60/5 563_EPOS4 Micro 24/5 564_EPOS4 Module 24/1.5 565_EPOS4 Compact 24/5 3-axes 566_EPOS4 Compact 24/1.5