


RE 13 Ø13 mm, precious metal brushes, 2 watt

RE



M 1:1

- Stock program
- Standard program
- Special program (on request)

Part numbers

118491 118492 118493 118494 118495 118496 118497 118498 118499 118500 118501 118502 118503 118504 118505

Motor data																
Values at nominal voltage																
1 Nominal voltage	V	1.5	1.5	1.8	2.4	3	3	3.6	4.2	4.8	6	7.2	9	10	12	15
2 No load speed	rpm	6570	6090	6380	7170	7100	6300	6800	6620	6490	6810	6590	6630	6840	7020	7150
3 No load current	mA	43.8	39.8	35.3	30.8	24.3	20.8	19.2	15.8	13.5	11.5	9.19	7.41	6.94	5.99	4.91
4 Nominal speed	rpm	5170	4320	4160	4400	3560	2550	3000	2880	2880	3130	2880	2940	3120	3330	3400
5 Nominal torque	mNm	1.46	1.58	1.82	2.18	2.78	2.91	2.85	2.91	3.02	2.95	2.93	2.94	2.92	2.93	2.88
6 Nominal current (max. continuous current)	A	0.72	0.72	0.72	0.72	0.72	0.669	0.592	0.502	0.446	0.367	0.294	0.237	0.218	0.188	0.151
7 Stall torque	mNm	6.22	5.12	5.01	5.5	5.51	4.86	5.1	5.16	5.46	5.49	5.26	5.34	5.42	5.63	5.54
8 Stall current	A	2.89	2.21	1.89	1.75	1.39	1.09	1.03	0.866	0.786	0.665	0.514	0.419	0.395	0.351	0.282
9 Max. efficiency	%	77	75	75	76	76	75	75	75	76	76	75	76	76	76	76
Characteristics																
10 Terminal resistance	Ω	0.519	0.679	0.951	1.37	2.16	2.75	3.5	4.85	6.11	9.03	14	21.5	25.3	34.2	53.2
11 Terminal inductance	mH	0.021	0.025	0.032	0.046	0.073	0.092	0.114	0.164	0.223	0.316	0.485	0.749	0.87	1.19	1.79
12 Torque constant	mNm/A	2.15	2.31	2.65	3.14	3.97	4.46	4.96	5.95	6.94	8.27	10.2	12.7	13.7	16	19.7
13 Speed constant	rpm/V	4440	4130	3610	3040	2410	2140	1930	1600	1380	1160	932	750	696	595	485
14 Speed / torque gradient	rpm/mNm	1070	1210	1300	1330	1310	1320	1360	1310	1210	1260	1270	1260	1280	1270	1310
15 Mechanical time constant	ms	7.65	7.55	7.45	7.37	7.28	7.27	7.28	7.23	7.16	7.2	7.21	7.21	7.21	7.22	7.27
16 Rotor inertia	gcm ²	0.681	0.596	0.548	0.53	0.53	0.526	0.512	0.528	0.565	0.545	0.541	0.544	0.536	0.543	0.529

Specifications

Thermal data

17 Thermal resistance housing-ambient 33 K/W

18 Thermal resistance winding-housing 7.0 K/W

19 Thermal time constant winding 4.88 s

20 Thermal time constant motor 229 s

21 Ambient temperature -20...+65°C

22 Max. winding temperature +85°C

Mechanical data (sleeve bearings)

23 Max. speed 11000 rpm

24 Axial play 0.05 - 0.15 mm

25 Radial play 0.014 mm

26 Max. axial load (dynamic) 0.8 N

27 Max. force for press fits (static) 15 N

(static, shaft supported) 95 N

28 Max. radial load, 5 mm from flange 1.4 N

Other specifications

29 Number of pole pairs 1

30 Number of commutator segments 7

31 Weight of motor 12 g

Operating range

n [rpm]

2.0 W

118501

M [mNm]

I [A]

Comments

Continuous operation

In observation of above listed thermal resistance (lines 17 and 18) the maximum permissible winding temperature will be reached during continuous operation at 25°C ambient.

= Thermal limit.

Short term operation

The motor may be briefly overloaded (recurring).

Assigned power rating

Modular system Details on catalog page 48

Sensor	Motor Control
498_ENX 13 GAMA	550_ESCON Module 24/2
501_ENX 13 IMR	550_ESCON 36/2 DC
532_Encoder MR 16 CPT	557_ESCON2 Nano 24/2
	563_EPOS4 Micro 24/5
	564_EPOS4 Module 24/1.5
	565_EPOS4 Compact 24/5 3-axes
	566_EPOS4 Compact 24/1.5