


EC-max 22 Ø22 mm, brushless, 25 watt



EC-max

- Stock program
- Standard program
- Special program (on request)

Part numbers

283856	283857	283858	283859	283860
--------	--------	--------	--------	--------

Motor Data

Values at nominal voltage						
1 Nominal voltage	V	12	18	24	36	48
2 No load speed	rpm	12400	12900	12900	12200	12900
3 No load current	mA	226	161	121	73.5	60.4
4 Nominal speed	rpm	9800	10300	10400	9630	10500
5 Nominal torque	mNm	23	21.8	22.7	22.5	23.2
6 Nominal current (max. continuous current)	A	2.71	1.8	1.4	0.872	0.716
7 Stall torque	mNm	114	112	121	111	127
8 Stall current	A	12.6	8.55	6.97	4	3.66
9 Max. efficiency	%	76	75	76	75	77
Characteristics						
10 Terminal resistance phase to phase	Ω	0.955	2.1	3.44	9.01	13.1
11 Terminal inductance phase to phase	mH	0.05	0.103	0.182	0.462	0.729
12 Torque constant	mNm/A	9.1	13	17.4	27.7	34.8
13 Speed constant	rpm/V	1050	732	549	345	274
14 Speed/torque gradient	rpm/mNm	110	118	109	112	103
15 Mechanical time constant	ms	5.14	5.5	5.06	5.23	4.82
16 Rotor inertia	gcm ²	4.45	4.45	4.45	4.45	4.45

Specifications

Thermal data	
17 Thermal resistance housing-ambient	10.2 K/W
18 Thermal resistance winding-housing	1.02 K/W
19 Thermal time constant winding	1.99 s
20 Thermal time constant motor	628 s
21 Ambient temperature	-40...+100°C
22 Max. winding temperature	+155°C

Mechanical data (preloaded ball bearings)	
23 Max. speed	18 000 rpm
24 Axial play at axial load	< 4 N 0 mm > 4 N 0.14 mm
25 Radial play	preloaded
26 Max. axial load (dynamic)	3.5 N
27 Max. force for press fits (static)	60 N
(static, shaft supported)	1000 N
28 Max. radial load, 5 mm from flange	16 N

Other specifications

29 Number of pole pairs	1
30 Number of phases	3
31 Weight of motor	110 g


Values listed in the table are nominal.

Connection (Cable AWG 24)

brown	Motor winding 1	Pin 1
red	Motor winding 2	Pin 2
orange	Motor winding 3	Pin 3
yellow	V _{Hall} 3...24 VDC	Pin 4
green	GND	Pin 5
blue	Hall sensor 1	Pin 6
violet	Hall sensor 2	Pin 7
grey	Hall sensor 3	Pin 8

Wiring diagram for Hall sensors see p. 67

Operating range



Comments

- Continuous operation**
In observation of above listed thermal resistance (lines 17 and 18) and an ambient temperature of 25°C, the maximum permissible winding temperature will be reached during continuous operation = thermal limit.
- Short term operation**
The motor may be briefly overloaded (recurring).
- Assigned power rating**

Modular system

1 Gear	420_GP 22 A
3 420_GP 22 HP	423_GP 32 C
110 g	429_GP 32 C
	435_KD 32
	472/473_GP 22 S
	474-482_GP 32 S

Sensor	
509_ENX 16 EASY	510_ENX 16 EASY XT
511_ENX 16 EASY Absolute	512_ENX 16 EASY Absolute XT

Accessories	
584_Brake AB 20	

Details on catalog page 52

Motor Control	
547_DEC Module 24/2	547_DEC Module 50/5
550_ESCON Module 24/2	551_ESCON 36/3 EC
551_ESCON Module 50/4 EC-S	551_ESCON Module 50/5
553_ESCON 50/5	557_ESCON2 Nano 24/2
557_ESCON2 Micro 60/5	563_EPOS4 Micro 24/5
564_EPOS4 Module 24/1.5	564_EPOS4 Module 50/5
565_EPOS4 Compact 24/5 3-axes	566_EPOS4 Compact 24/1.5
567_EPOS4 Compact 50/5	569_EPOS4 50/5