


EC-i 52 Ø52 mm, brushless, 250 watt

open housing

EC-i



M 1:2

- Stock program
- Standard program
- Special program (on request)

Part numbers

	with Hall sensors	667060	667061	667062	667063
--	-------------------	--------	--------	--------	--------

Motor data

Values at nominal voltage					
1 Nominal voltage	V	18	24	36	48
2 No load speed	rpm	4450	4860	5010	5090
3 No load current	mA	829	707	493	379
4 Nominal speed	rpm	3770	4140	4280	4370
5 Nominal torque	mNm	596	612	646	623
6 Nominal current (max. continuous current)	A	14.7	12.3	8.86	6.55
7 Stall torque	mNm	4290	4560	4860	4830
8 Stall current	A	273	278	232	174
9 Max. efficiency	%	89.1	90	90.8	90.7
Characteristics					
10 Terminal resistance phase to phase	Ω	0.0658	0.0863	0.155	0.276
11 Terminal inductance phase to phase	mH	0.0826	0.123	0.261	0.45
12 Torque constant	mNm/A	38.2	46.7	68	89.2
13 Speed constant	rpm/V	250	204	140	107
14 Speed/torque gradient	rpm/mNm	0.43	0.377	0.32	0.331
15 Mechanical time constant	ms	0.765	0.671	0.57	0.59
16 Rotor inertia	gcm ²	170	170	170	170


Specifications

- Thermal data**
- 17 Thermal resistance housing-ambient 3.5 K/W
 - 18 Thermal resistance winding-housing 0.526 K/W
 - 19 Thermal time constant winding 13.7 s
 - 20 Thermal time constant motor 1310 s
 - 21 Ambient temperature -40...+100°C
 - 22 Max. winding temperature +155°C

Mechanical data (preloaded ball bearings)

- 23 Max. speed 6000 rpm
- 24 Axial play at axial load < 9.0 N 0 mm
- 25 Radial play 0.14 mm
- 26 Max. axial load (dynamic) 12 N
- 27 Max. force for press fits (static) 150 N
- 28 Max. radial load, 5 mm from flange 6000 N

Operating range



- Continuous operation
- Continuous operation with reduced thermal resistance R_{th2} 50%
- Intermittent operation
- Assigned power rating

Other specifications

- 29 Number of pole pairs 8
- 30 Number of phases 3
- 31 Weight of motor 750 g

Values listed in the table are nominal.

Connection motor (Cable AWG 14)

- red Motor winding 1 Pin 1
- black Motor winding 2 Pin 2
- white Motor winding 3 Pin 3
- N.C. Pin 4

Connector Article number

- Molex 171692-0104

Connection sensor (Cable AWG 26)

- yellow Hall sensor 1 Pin 1
- brown Hall sensor 2 Pin 2
- grey Hall sensor 3 Pin 3
- blue GND Pin 4
- green V_{Hall} 4.5...24 VDC Pin 5
- N.C. Pin 6

Connector Article number

- Molex 430-25-0600

Wiring diagram for Hall sensors see p. 69

Modular system

- Sensor**
- 509_ENX 16 EASY
 - 510_ENX 16 EASY XT
 - 511_ENX 16 EASY Absolute
 - 512_ENX 16 EASY Absolute XT
 - 519_ENX 16 RIO

Details on catalog page 52

- Motor Control**
- 552_ESCON Module 50/8 HE
 - 553_ESCON 70/10
 - 558_ESCON2 Module 60/30
 - 559_ESCON2 Compact 60/30
 - 565_EPOS4 Module 50/8
 - 565_EPOS4 Module 50/15
 - 567_EPOS4 Compact 50/8
 - 568_EPOS4 Compact 50/15
 - 569_EPOS4 70/15
 - 570_EPOS4 Disk 60/8
 - 571_EPOS4 Disk 60/12