


ENX



Selection criteria	EASY absolute differential	
Speed and rotation direction detection	■	
Speed and position control	■	
Compact and robust design	■	
High resolution	■	
Cost effective	▲	

Variables	For configurable units	Non-configurable units
Part Number	depends on configuration	588632 588631
Signal protocol	BiSS-C, SSI	BiSS-C SSI
Cable length mm	500, 1000	500 500
Alignment of cable outlet in relation to motor flange °	15 (pitch)	0 0

Technical drawing of a metal fitting. The side view shows a cylindrical body with a diameter of $\varnothing 15.8$ mm and a width of 9 mm. A dashed line indicates a horizontal centerline. Below the side view is a top view showing a flange with two mounting tabs and a bracket-like structure on the right side.

© 2025 maxon. All rights reserved. February edition. Subject to change.